



ATA630009016

Trunking 6x32,traffic white

Technical Features

Dimensions

| | |
|---------------------|---------------------------|
| Height | 6 mm |
| Width | 32 mm |
| Length | 2100 mm |
| Inner cross-section | 170 - 170 mm ² |

Capacity

| | |
|--|---|
| Max. number of cables (Ø11mm, 50% filled, without devices) | 0 |
|--|---|

Materials

| | |
|-----------|-------------------------|
| Material | Polyvinylchloride (PVC) |
| Treatment | Untreated |
| RAL code | 9016 |
| Colour | Traffic white |

Safety

| | |
|-------------------------------|------|
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP40 |

Standards

| | |
|---|----|
| Suitable for functional integrity according to DIN4102-12 | No |
|---|----|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 65 °C |
|-----------------------|------------|

Connectivity

| | |
|-------------------|------------------|
| Trunking coupling | Without coupling |
|-------------------|------------------|

Equipment

| | |
|--------------------------------|----|
| Number of partitions | 0 |
| Number of pluggable partitions | 0 |
| Cable retaining clip included | No |
| With protective film | No |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |