



VU24IE

Encl.,Volta,flush,2x12MOD,IP30,Version ireland

### Technical Features

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

#### Installation, mounting

|                            |    |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

#### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

#### Power

|                                                  |         |
|--------------------------------------------------|---------|
| Maximum power loss per cabinet at $\Delta T=20K$ | 17.50 W |
|--------------------------------------------------|---------|

#### Equipment

|                 |   |
|-----------------|---|
| Number of rails | 2 |
|-----------------|---|

|                |   |
|----------------|---|
| Number of rows | 2 |
|----------------|---|

|                            |   |
|----------------------------|---|
| Number of section in width | 1 |
|----------------------------|---|

|           |    |
|-----------|----|
| With lock | No |
|-----------|----|

|                            |    |
|----------------------------|----|
| Has neutral terminal block | No |
|----------------------------|----|

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 24 |
|-------------------|----|

|                                           |    |
|-------------------------------------------|----|
| Number of half modules terminals per rail | 48 |
|-------------------------------------------|----|

#### Functions

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

#### Dimensions

|        |           |
|--------|-----------|
| Height | 505.50 mm |
|--------|-----------|

|       |        |
|-------|--------|
| Width | 348 mm |
|-------|--------|

|       |          |
|-------|----------|
| Depth | 94.50 mm |
|-------|----------|

|                 |        |
|-----------------|--------|
| Built-in height | 490 mm |
|-----------------|--------|

|                |        |
|----------------|--------|
| Built-in width | 335 mm |
|----------------|--------|

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

#### Dimensions

|                |       |
|----------------|-------|
| Built-in depth | 90 mm |
|----------------|-------|

#### Cover, door

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

#### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

#### Materials

|          |         |
|----------|---------|
| Material | Plastic |
|----------|---------|

|          |      |
|----------|------|
| RAL code | 9010 |
|----------|------|

|        |            |
|--------|------------|
| Colour | Pure white |
|--------|------------|

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

|                    |    |
|--------------------|----|
| Has mounting plate | No |
|--------------------|----|

|                               |                              |
|-------------------------------|------------------------------|
| <b>Materials</b>              |                              |
| Ultraviolet-resistant         | Yes                          |
| <b>Safety</b>                 |                              |
| Protection class              | Isolation class II           |
| Ingress Protection (IP) class | IP30                         |
| Locking type                  | Snap on lock<br>Without lock |
| Glow wire test                | 650 °C                       |
| <b>Sustainability</b>         |                              |
| RoHS conform                  | Yes                          |