



3037

Intermediate switch, light control

Technical Features

Electric current

Switching current	10 AX (100W LED (SBL))
-------------------	------------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Surface finish	Matt
Material	Metal Plastic

Identification

Assembly arrangement	Basic element
----------------------	---------------

Connectivity

Mounting type	Claw mounting
---------------	---------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	71 x 71 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	10 A
---------------	------

Texts

Installation mode	With spreader claws
Type of connection	With plug-in terminals
Lighting	For lighting and monitoring circuit
Switch mode	Intermediate