



3036

**Change-over switch 10AX 250V~, Light control**

**Technical Features**

<b>Electric current</b>	
Switching current	10 AX (100W LED (SBL))
<b>Installation, mounting</b>	
Mounting on	Flush mounting
<b>Voltage</b>	
Rated voltage	250 V
<b>Frequency</b>	
Frequency	50 - 60 Hz
<b>Materials</b>	
Surface finish	Matt
Material	Metal Plastic
<b>Identification</b>	
Assembly arrangement	Basic element
<b>Connectivity</b>	
Mounting type	Claw mounting
<b>Controls and indicators</b>	
Number of buttons	1
<b>Dimensions</b>	
Dimensions	71 x 71 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm
<b>Safety</b>	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK07
<b>Architecture</b>	
Control/operation element	Single rocker
<b>Electric current</b>	
Rated current	10 A
<b>Texts</b>	
Installation mode	With spreader claws For screw fastening
Type of connection	With plug-in terminals
Lighting	For lighting and monitoring circuit
Switch mode	Off/change-over
<b>Sustainability</b>	
Halogen free	Yes
RoHS conform	Yes