



3036

Change-over switch 10AX 250V~, Light control

Technical Features

Electric current

Switching current 10 AX (100W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Surface finish Matt

Material Metal
Plastic

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Claw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 71 x 71 mm

Built-in depth 31 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Impact resistance IK IK07

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Texts

Installation mode With spreader claws
For screw fastening

Type of connection With plug-in terminals

Lighting For lighting and monitoring circuit

Switch mode Off/change-over

Sustainability

Halogen free Yes

RoHS conform Yes