



ESL463

**Contactor 63A, 4NO, 12V~50Hz**

**Technical Features**

**Connection**

|                  |     |
|------------------|-----|
| Type of contacts | 4NO |
|------------------|-----|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

**Voltage**

|   |             |
|---|-------------|
| Rated impulse withstand voltage $U_{imp}$ | 4000 V      |
| Rated insulation voltage $U_i$            | 440 V       |
| Rated operational voltage $U_e$           | 400 - 400 V |
| Command voltage AC                        | 12 - 12 V   |
| Command voltage DC                        | 0 - 0 V     |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10 - 50 °C |
|-----------------------|-------------|

**Use**

|                 |             |
|-----------------|-------------|
| Category of use | AC-7a/AC-7b |
|-----------------|-------------|

**Use conditions**

|                               |             |
|-------------------------------|-------------|
| Storage/transport temperature | -40 - 80 °C |
|-------------------------------|-------------|

**Endurance**

|  |        |
|--|--------|
| Number of mechanical operations        | 100000 |
| Electric endurance in number of cycles | 30000  |

**Power**

|                           |         |
|---------------------------|---------|
| Total power loss under IN | 24.50 W |
| Inrush power absorbed     | 5.20 VA |

**Dimensions**

|        |       |
|--------|-------|
| Height | 85 mm |
| Width  | 54 mm |
| Depth  | 60 mm |

**Connection**

|                    |   |
|--------------------|---|
| Number of contacts | 4 |
|--------------------|---|

**Equipment**

|                               |    |
|-------------------------------|----|
| Number of NO contacts         | 4  |
| Number of NC contacts         | 0  |
| With switch for manual switch | No |

**Connection**

|                                  |                          |
|----------------------------------|--------------------------|
| Cross-section flexible conductor | 1.5 - 16 mm <sup>2</sup> |
| Cross-section rigid conductor    | 1.5 - 25 mm <sup>2</sup> |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|