
Product Datasheet
3031



3031

Rocker switch off, Module inserts

Technical Features

Electric current	
Switching current	10 AX (100W LED (SBL))
Installation, mounting	
Mounting on	Flush mounting
Voltage	
Rated voltage	250 V
Frequency	
Frequency	50 - 60 Hz
Materials	
Material	Metal Plastic
Identification	
Assembly arrangement	Basic element
Connectivity	
Mounting type	Claw mounting
Controls and indicators	
Number of buttons	1
Dimensions	
Dimensions	70.80 x 70.80 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm
Safety	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK07
Architecture	
Control/operation element	Single rocker
Electric current	
Rated current	10 A
Connection	
Connector/plug type	Plug clamp
Texts	
Installation mode	With spreader claws For screw fastening
Type of connection	With plug-in terminals
Lighting	For lighting and monitoring circuit
Switch mode	Off