



3035

## Series switch

### Technical Features

#### Electric current

Switching current 10 AX (100W LED (SBL))

#### Installation, mounting

Mounting on Flush mounting

#### Voltage

Rated voltage 250 V

#### Frequency

Frequency 50 - 60 Hz

#### Materials

Surface finish Matt

Material Metal  
Plastic

#### Identification

Assembly arrangement Basic element

#### Connectivity

Mounting type Claw mounting

#### Controls and indicators

Number of buttons 2

#### Dimensions

Dimensions 71 x 71 mm

Built-in depth 32 mm

Built-in depth flush-mounted boxes 35 mm

#### Safety

Ingress Protection (IP) class IP20

Impact resistance IK IK07

#### Architecture

Control/operation element Double rocker

#### Electric current

Rated current 10 A

#### Connection

Connector/plug type Plug-in terminal

#### Texts

Installation mode With spreader claws

Type of connection With plug-in terminals

Lighting For lighting and monitoring circuit

Switch mode Series

#### Sustainability

Halogen free Yes

RoHS conform Yes