

Product Datasheet

HFD440



HFD440

Fuse comb. switch 4P - 400 A / T2

Technical Features

Electric current

Rated current	400 A
---------------	-------

Architecture

Number of poles	4
Control/operation element	Door coupling rotary drive

Voltage

Rated insulation voltage Ui	800 V
-----------------------------	-------

Power

Total power loss under IN	229.60 W
---------------------------	----------

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Fuse

Fuse size	NH2
-----------	-----

Dimensions

Height	240 mm
Width	325 mm

Power

Power loss per pole at In	57.40 W
Rated operational power under 400 V AC AC1	263000 W

Cover, door

Interlockable	Yes
---------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes