



75010016

**Technical Features**

**Equipment**

Web server	No
------------	----

**Voltage**

Operating voltage	24 - 24 V
Operating voltage over bus	21 - 32 V

**Connectivity**

Type of interface bus system/media gateway	Ethernet interface
--	--------------------

**Settings**

Supported configuration mode	ETS
------------------------------	-----

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Controls and indicators**

With LED indication	Yes
---------------------	-----

**Dimensions**

Width	36 mm
Dimensions	90 x 36 mm
Depth	58 mm

**Connection**

Connector/plug type	DRA (DIN-rail Adapter)
---------------------	------------------------

**Texts**

Type of connection	Operating voltage connection via connecting terminal With RJ45 connection for Ethernet/IP networks Line connection via connecting terminal
--------------------	--

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes