



WMPS12RB

#### Push Switch with Bell Symbol

##### Technical Features

###### Electric current

Switching current	10 A
Momentary contact current	10 A

###### Voltage

Rated voltage	250 V
---------------	-------

###### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Architecture

Number of poles	2
-----------------	---

##### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated
Transparent	No

##### Dimensions

Height	86 mm
Width	86 mm
Depth	24 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Accessories

Has labelling field	No
---------------------	----

##### Texts

Imprint	Without imprint
Installation mode	For flush-mounted and hollow wall mounting
Switch mode	NO contact

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes