



HFD425

Fuse comb. switch 4P - 250 A / T1

Technical Features

Electric current

Rated current 250 A

Architecture

Number of poles 4

Control/operation element Door coupling rotary drive

Voltage

Rated insulation voltage U_i 750 V

Power

Total power loss under I_N 164.40 W

Safety

Ingress Protection (IP) class IP00

Fuse

Fuse size NH1

Dimensions

Height 195 mm

Width 294 mm

Power

Power loss per pole at I_n 41.10 W

Rated operational power under 400 V AC AC1 164000 W

Cover, door

Interlockable Yes

Sustainability

REACH-SVHC free Yes

RoHS conform Yes