

Product Datasheet

WGDL122NNB



WGDL122NNB

16AX 2G 2W switch with led;nb

Technical Features

Electric current	
Switching current	16 A

Voltage	
Rated voltage	250 V

Materials	
Colour	Bronze
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

Controls and indicators	
Number of buttons	2

Dimensions	
Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm

Safety	
Ingress Protection (IP) class	IP20

Architecture	
Control/operation element	Double rocker

Electric current	
Rated current	16 A

Texts	
Switch mode	2-way

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes