



HFD406

Fuse comb. switch 4P - 63 A / T000

Technical Features

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	4
Control/operation element	Door coupling rotary drive

Voltage

Rated insulation voltage U_i	750 V
--------------------------------	-------

Power

Total power loss under I_N	33.60 W
------------------------------	---------

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Fuse

Fuse size	NH000
-----------	-------

Dimensions

Height	118 mm
Width	168 mm

Power

Power loss per pole at I_n	8.40 W
Rated operational power under 400 V AC AC1	41000 W

Cover, door

Interlockable	Yes
---------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes