



HIC425E

ATS with energy management 4x 2500A

Technical Features

Voltage

Rated operational voltage U_e 380 - 415 V

Electric current

Rated current 2500 A

Power

Rated operational power under 400 V AC AC1 1645000 W

Architecture

Number of poles 4

Device construction type Fixed built-in

Compatibility

Suitable for DIN Rail Yes

Suitable for distribution board Yes