



TYF784



**Analog input device 4-gang KNX**

**Technical Features**

**Voltage**

Operating voltage over bus 21 - 32 V

**Settings**

Supported configuration mode ETS

**Voltage**

Auxiliary tension 24 - 24 V

**Frequency**

Frequency 50 - 60 Hz

**Power**

Current consumption 170 mA

**Use conditions**

Operating temperature -5 - 45 °C

**Capacity**

Number of modules 4

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes