



WBWP2SH

Socket IP53 Twin horizontal 10A Shallow mount

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

| | |
|----------------|------------------------|
| Colour | Light grey |
| Surface finish | Glossy |
| Material | Glass Thermoplastic |
| Treatment | Untreated |

Dimensions

| | |
|--------|--------|
| Height | 85 mm |
| Width | 115 mm |
| Depth | 75 mm |

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type | Screw mounting |

Equipment

| | |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert | No |
| With hinged lid | No |
| With round protective earth pin | No |
| With signal lamp | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Safety

| | |
|-------------------------------|------|
| Impact resistance IK | IK08 |
| Ingress Protection (IP) class | IP53 |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Identification

| | |
|--------------|----|
| With imprint | No |
|--------------|----|

Texts

| | |
|--------------------|-------------------------------------|
| Cover | Complete housing |
| Protection | Without enhanced contact protection |
| Type of connection | With screw terminals |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |