



HIC425G

**Automatic transfer switch 4x 2500A**

**Technical Features**

**Voltage**

Rated operational voltage U<sub>e</sub> 380 - 415 V

**Electric current**

Rated current 2500 A

**Power**

Rated operational power under 400 V AC AC1 1645000 W

**Architecture**

Number of poles 4

Device construction type Fixed built-in

**Compatibility**

Suitable for DIN Rail No

Suitable for distribution board Yes

**Installation, mounting**

Mounting on Mounting plate