



LF6006009010

Trunking from PVC LF 60x60mm pure white

Technical Features

Dimensions

Height	60 mm
Width	57 mm
Length	2000 mm
Inner cross-section	2690 - 2690 mm ²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	12
--	----

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9010
Colour	Pure white

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP30

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Equipment

Number of partitions	0
Number of compartments	1 - 2
Number of pluggable partitions	1
Cable retaining clip included	Yes
With protective film	No

Illustrations | Drawings

