



HIC425G

**Automatic transfer switch 4x 1250A**

**Technical Features**

**Voltage**

Rated operational voltage U <sub>e</sub>	380 - 415 V
--	-------------

**Electric current**

Rated current	1250 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	100 kA

**Power**

Rated operational power under 400 V AC AC1	822000 W
--	----------

**Architecture**

Number of poles	4
Device construction type	Fixed built-in

**Compatibility**

Suitable for DIN Rail	No
Suitable for distribution board	Yes

**Installation, mounting**

Mounting on	Mounting plate
-------------	----------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes