



HFD312

Fuse comb. switch 3P - 125 A /T00

Technical Features

Electric current

Rated current	125 A
---------------	-------

Architecture

Number of poles	3
Control/operation element	Door coupling rotary drive

Voltage

Rated insulation voltage U_i	750 V
--------------------------------	-------

Power

Total power loss under I_N	60.90 W
------------------------------	---------

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Fuse

Fuse size	NH00
-----------	------

Dimensions

Height	162 mm
Width	148 mm

Power

Power loss per pole at I_n	20.30 W
Rated operational power under 400 V AC AC1	82000 W

Cover, door

Interlockable	Yes
---------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes