



HFD325

**Fuse comb. switch 3P - 250 A / T1**

**Technical Features**

**Electric current**

Rated current	250 A
---------------	-------

**Architecture**

Number of poles	3
Control/operation element	Door coupling rotary drive

**Voltage**

Rated insulation voltage $U_i$	750 V
--------------------------------	-------

**Power**

Total power loss under $I_N$	123.30 W
------------------------------	----------

**Safety**

Ingress Protection (IP) class	IP00
-------------------------------	------

**Fuse**

Fuse size	NH1
-----------	-----

**Dimensions**

Height	195 mm
Width	234 mm

**Power**

Power loss per pole at $I_n$	41.10 W
Rated operational power under 400 V AC AC1	164000 W

**Cover, door**

Interlockable	Yes
---------------	-----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes