



HFD325

Fuse comb. switch 3P - 250 A / T1

Technical Features

Electric current

Rated current	250 A
---------------	-------

Architecture

Number of poles	3
Control/operation element	Door coupling rotary drive

Voltage

Rated insulation voltage U_i	750 V
--------------------------------	-------

Power

Total power loss under I_N	123.30 W
------------------------------	----------

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Fuse

Fuse size	NH1
-----------	-----

Dimensions

Height	195 mm
Width	234 mm

Power

Power loss per pole at I_n	41.10 W
Rated operational power under 400 V AC AC1	164000 W

Cover, door

Interlockable	Yes
---------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes