

# Product Datasheet

## HFD325



HFD325

### Fuse comb. switch 3P - 250 A / T1

#### Technical Features

##### Electric current

Rated current	250 A
---------------	-------

##### Architecture

Number of poles	3
Control/operation element	Door coupling rotary drive

##### Voltage

Rated insulation voltage Ui	750 V
-----------------------------	-------

##### Power

Total power loss under IN	123.30 W
---------------------------	----------

##### Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

##### Fuse

Fuse size	NH1
-----------	-----

##### Dimensions

Height	195 mm
Width	234 mm

##### Power

Power loss per pole at In	41.10 W
Rated operational power under 400 V AC AC1	164000 W

##### Cover, door

Interlockable	Yes
---------------	-----

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes