



28807006

Radio Touch and loudspeaker K.1 anthracite, matt

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 60 Hz
Radio reception frequency	87.5 - 108.0 MHz

Materials

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Treatment	Varnished

Dimensions

Height	70.80 mm
Width	141.60 mm
Depth	46.50 mm
Built-in depth	33 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Connection

Cross-section loudspeaker	1.50 - 1.50 mm ²
Conductor cross-section	2.50 - 2.50 mm ²

Functions

Integrated DCF clock	Yes
----------------------	-----

Equipment

Type of display	Digital
-----------------	---------

Texts

Type of connection	With screw terminals
Junction	With 2 loudspeaker connections
Installation mode	Screw fastening via supporting plate Single and combination mounting
Function	Alarm clock with snooze function Sleep timer Countdown Volume control
Extension unit input	Extension unit input for separate on/off switching