



TYF616

**Module multi applications 16 outputs**

**Technical Features**

**Connectivity**

With bus system KNX	Yes
With bus system KNX radio	No

**Dimensions**

Dimensions	90 x 171 mm
Height	90 mm
Width	171 mm
Depth	64 mm
Number of width units	10

**Electric current**

Rated current	10 A
---------------	------

**Materials**

Colour	Light grey
--------	------------

**Equipment**

Radio frequency bidirectional	No
With switch for manual switch	Yes

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Output power	2300 W
--------------	--------

**Voltage**

Rated operational voltage Ue	195 - 255 V
System supply voltage	30 V DC Via bus
Operating voltage over bus	21 - 32 V

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Connection**

Cross-section flexible conductor	0.75 - 4 mm <sup>2</sup>
----------------------------------	--------------------------