



389303

Rotary switch, 2p off, S1930/Glas/R.clas

Technical Features

Electric current

Switching current 10 AX (100W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Material Duroplastic

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Claw mounting

Dimensions

Dimensions 71 x 71 mm

Built-in depth 31 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Short rotary handle

Electric current

Rated current 10 A

Texts

Installation mode With spreader claws

Type of connection With screw terminals

Lighting Without neon lamp

Switch mode 2-pole off