



BS264

Earth leakage add-on block 2P 63A 1A AC S Class

Technical Features

Voltage	
Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency	
Frequency	50 - 50 Hz

Electric current	
Rated residual operating current Idn	1000 mA
Rated current	63 A

Architecture	
Number of poles	2
Neutral position	Left

Capacity	
Number of modules	2

Connectivity	
Down connection alignment for modular devices	Aligned terminal

Dimensions	
Height	70 mm
Width	35 mm
Depth	92 mm

Illustrations | Drawings

