



29536084



**LED signal light, white lighting Q.x alu velvety, lacquered**

**Technical Features**

**Voltage**

Rated voltage 230 V

**Power**

Power absorbed 1 W

**Frequency**

Frequency 50 - 60 Hz

**Lighting**

Type of lamp LED

**Materials**

Colour Aluminium

RAL code 9006

Surface finish Velvety

Material Metal  
Plastic

Treatment Varnished

**Dimensions**

Height 70 mm

Width 70 mm

Depth 50 mm

**Connection**

Conductor cross-section 2.50 - 2.50 mm<sup>2</sup>

**Connectivity**

Mounting type Claw mounting  
Screw connection

**Safety**

Ingress Protection (IP) class IP20

**Texts**

Lighting Light colour cold white

Labelling Foils with imprint of symbols insertable

Imprint Without imprint

**Suitable for**

Q.x

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes