



LFF4004009016

Trunking with coupling tehalit.LFF 40x40mm traffic white

Technical Features

Dimensions

Height	40 mm
Width	40 mm
Length	2000 mm
Inner cross-section	1200 - 1200 mm ²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	6
--	---

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9016
Colour	Traffic white

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Equipment

Number of partitions	0
Number of pluggable partitions	0
Cable retaining clip included	No
With protective film	No

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes