



VML11010

Consumer unit, Design10, dual row, 20+20way, 100A switch disconnecter incomer

### Technical Features

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Architecture

Number of poles	2
-----------------	---

#### Functions

Has protection main switch	Yes
Overvoltage protection	No

#### Capacity

Number of modules	40
-------------------	----

#### Electric current

Rated current	100 A
---------------	-------

#### Dimensions

Depth	100 mm
Height	485 mm
Width	476 mm
Thickness of sidewall	1 mm

#### Cover, door

Interlockable	No
Door/cover is transparent	No

#### Materials

RAL code	9010
Colour	Pure white
Material	Steel

#### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

#### Connection

Number of accessible phases	1
-----------------------------	---

#### Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

#### Equipment

Number of rows	2
Number of rails	2
Extension possible	No

#### Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes