



VML11010

Consumer unit, Design10, dual row, 20+20way, 100A switch disconnecter incomer

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Architecture**

Number of poles 2

**Functions**

Has protection main switch Yes

Overvoltage protection No

**Installation, mounting**

Suitable for outdoor usage No

**Capacity**

Number of modules 40

**Electric current**

Rated current 100 A

**Dimensions**

Depth 100 mm

Height 485 mm

Width 476 mm

Thickness of sidewall 1 mm

**Cover, door**

Interlockable No

Door/cover is transparent No

**Materials**

RAL code 9010

Colour Pure white

Material Steel

**Connection**

Number of accessible phases 1

**Scope of delivery**

Number of RCCB in enclosure 0

**Equipment**

Number of rows 2

Number of rails 2

Extension possible No

With socket outlet No

**Safety**

Impact resistance IK IK05

Ingress Protection (IP) class IP2XC

Number of earth leakage switches 300 mA 0

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes