



41108914



SCHUKO soc.out. LED+ZSV impr.,labfield,enhncd contact prot. S1/B3/7

#### Technical Features

##### Voltage

Rated voltage 250 V

##### Electric current

Rated current 16 A

##### Frequency

Frequency 50 - 60 Hz

##### Materials

Colour Orange

RAL code 2003

Surface finish Glossy

Material Duroplastic

Treatment Untreated

##### Dimensions

Height 71 mm

Width 71 mm

Built-in depth flush-mounted boxes 31 mm

Built-in depth 32 mm

##### Installation, mounting

Mounting on Flush mounting

##### Connectivity

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

##### Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

##### Accessories

Has labelling field Yes

##### Capacity

Number of modules 1

##### Controls and indicators

Type of lighting for the installation devices Integrated operating control light

##### Safety

With enhanced contact protection Yes

Impact resistance IK IK02

Ingress Protection (IP) class IP20

##### Functions

With orientation lighting No

With function lighting Yes

##### Texts

Imprint With imprint "ZSV"

Cover Central cover plate

---

**Texts**

Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

---

**Suitable for**

S.x/B.x

---

**Sustainability**

Halogen free	Yes
RoHS conform	Yes