



TXB344



IP20



Binary input 4 fold + LED output 4 fold, flush mounted, KNX

Technical Features

Architecture

Bus system	EIB
------------	-----

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Electric current

Number of entry circuits	4
--------------------------	---

Equipment

External signal voltage necessary	Yes
-----------------------------------	-----

Connectivity

With bus system KNX radio	No
---------------------------	----

Equipment

Radio frequency bidirectional	No
-------------------------------	----

With battery	No
--------------	----

With HVAC control	No
-------------------	----

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Lighting

LED controlling	Yes
-----------------	-----

Materials

Material	Polyamide (PA)
----------	----------------

Colour	Light grey
--------	------------

RAL code	7035
----------	------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Voltage

Input voltage	5 - 5 V
---------------	---------

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Type voltage supply	DC
---------------------	----

System supply voltage	30 V DC Via bus
-----------------------	-----------------

Texts

Installation mode	For flush-mounted and hollow wall mounting
-------------------	--

Type of connection	With pre-assembled cable
--------------------	--------------------------

Sustainability

RoHS conform	Yes
--------------	-----