



41108913



## SCHUKO soc.out. LED+"SV" impr.,labfield,enhncd contact prot., S1/B3/7een

### Technical Features

#### Electric current

Rated current	16 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Green
RAL code	6029
Surface finish	Glossy
Material	Duroplastic
Treatment	Untreated

#### Dimensions

Height	71 mm
Width	71 mm
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

#### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	Yes
---------------------	-----

#### Capacity

Number of modules	1
-------------------	---

#### Controls and indicators

Type of lighting for the installation devices	Integrated operating control light
---	------------------------------------

#### Safety

With enhanced contact protection	Yes
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

#### Functions

With orientation lighting	No
With function lighting	Yes

#### Texts

Imprint	With imprint "SV"
Cover	Central cover plate

Product Datasheet

41108913

Texts	
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals
Suitable for	
S.x/B.x	
Sustainability	
RoHS conform	Yes