

# Product Datasheet

## TXB322



TXB322



Binary input 2 fold + LED output 2 fold, flush mounted, KNX

### Technical Features

#### Architecture

Bus system	EIB
------------	-----

#### Settings

Supported configuration mode	ETS easy
------------------------------	-------------

#### Electric current

Number of entry circuits	2
--------------------------	---

#### Equipment

External signal voltage necessary	Yes
-----------------------------------	-----

#### Connectivity

With bus system KNX radio	No
---------------------------	----

#### Equipment

Radio frequency bidirectional	No
With battery	No
With HVAC control	No

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Lighting

LED controlling	Yes
-----------------	-----

#### Materials

Material	Polyamide (PA)
Colour	Light grey
RAL code	7035

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

#### Voltage

Input voltage	5 - 5 V
Operating voltage over bus	21 - 32 V
Type voltage supply	DC
System supply voltage	30 V DC Via bus

#### Texts

Installation mode	For flush-mounted and hollow wall mounting
Type of connection	With pre-assembled cable

#### Sustainability

RoHS conform	Yes
--------------	-----