



TXB322



**Binary input 2 fold + LED output 2 fold, flush mounted, KNX**

**Technical Features**

**Architecture**

Bus system

EIB

**Settings**

Supported configuration mode

ETS  
easy

**Electric current**

Number of entry circuits

2

**Equipment**

External signal voltage necessary

Yes

**Connectivity**

With bus system KNX radio

No

**Equipment**

Radio frequency bidirectional

No

With battery

No

With HVAC control

No

**Installation, mounting**

Mounting on

Flush mounting

**Lighting**

LED controlling

Yes

**Materials**

Material

Polyamide (PA)

Colour

Light grey

RAL code

7035

**Safety**

Ingress Protection (IP) class

IP20

**Use conditions**

Operating temperature

0 - 45 °C

**Voltage**

Input voltage

5 - 5 V

Operating voltage over bus

21 - 32 V

Type voltage supply

DC

System supply voltage

30 V DC Via bus

**Texts**

Installation mode

For flush-mounted and hollow wall mounting

Type of connection

With pre-assembled cable

**Sustainability**

RoHS conform

Yes