



41108982



SCHUKO soc.out. LED,labfield,enhncd contact prot.,screw-in lift term.,S1,wh

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour White

RAL code 1013

Surface finish Glossy

Material Duroplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field Yes

Capacity

Number of modules 1

Controls and indicators

Type of lighting for the installation devices Integrated operating control light

Safety

With enhanced contact protection Yes

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting Yes

Identification

With imprint No

Texts

Cover Central cover plate

Protection Enhanced contact protection

Type of connection With screw-in lift terminals

Suitable for

S.x/B.x

Sustainability

Halogen free

Yes

RoHS conform

Yes
