



WPSS81W

**1 Gang Double Pole Switched Socket White**

**Technical Features**

**Electric current**

Rated current	13 A
---------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

Nominal voltage	250 - 250 V
-----------------	-------------

**Materials**

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Steel
----------	-------

Treatment	Epoxy
-----------	-------

**Dimensions**

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Depth	26 mm
-------	-------

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

Mounting-/Connection Position	Horizontal
-------------------------------	------------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	0
-------------------	---

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Functions**

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

**Texts**

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
-------	------------------

Wiring	With earth connection
--------	-----------------------

Protection	Enhanced contact protection
------------	-----------------------------

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----