



VML\_SIZE\_7

**Design 10 Consumer Unit 20 Way 100A Sw Disconnector Incomer Round KO**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
----------------------------	-----

Overvoltage protection	No
------------------------	----

**Capacity**

Number of modules	20
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	100 mm
-------	--------

Height	98.20 mm
--------	----------

Width	476 mm
-------	--------

Thickness of sidewall	1 mm
-----------------------	------

**Cover, door**

Interlockable	No
---------------	----

Door/cover is transparent	No
---------------------------	----

**Materials**

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Material	Steel
----------	-------

**Installation, mounting**

Suitable for outdoor usage	No
----------------------------	----

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	0
-----------------------------	---

**Equipment**

Number of rows	1
----------------	---

Number of rails	1
-----------------	---

Extension possible	No
--------------------	----

**Safety**

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----