




414521

SCHUKO soc.out.,mounting orient. var. in 45°step,screw-in lift ,1930/glass,bl.

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	16 A
---------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Black
RAL code	9005
Surface finish	Glossy
Material	Duroplastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	Yes
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts	
Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for	
Serie 1930 / Serie Glas	

Sustainability	
Halogen free	Yes
RoHS conform	Yes