

# Product Datasheet

## WPDP50N



WPDP50N

### 50A Double Pole Switch 1 Gang with LED Indicator

#### Technical Features

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Materials

|                |        |
|----------------|--------|
| Colour         | Grey   |
| Surface finish | Glossy |
| Material       | Steel  |
| Treatment      | Epoxy  |

##### Identification

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

##### Dimensions

|                |            |
|----------------|------------|
| Dimensions     | 86 x 86 mm |
| Built-in depth | 21.20 mm   |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 50 A |
|---------------|------|

##### Texts

|             |                         |
|-------------|-------------------------|
| Lighting    | With control LED for ON |
| Switch mode | 2-pole                  |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|