



WRDP84FOPSB

## 20A Double Pole Switch with Flex Outlet Polished Steel Black Insert

### Technical Features

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Dimensions	86 x 86 mm
Built-in depth	20 mm

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Single rocker
---------------------------	---------------

#### Electric current

Rated current	20 A
---------------	------

#### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes