



VF412TT2

Small distributor,golf,flush,4row,IP40,48M,MS-terminal,ANZ,N+PE,transparent door

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Flush mounting

Electric current

Rated current 80 A

Equipment

Number of rails 4

Number of rows 4

Number of section in width 1

With lock No

Has neutral terminal block Yes

Capacity

Number of modules 48

Functions

With conduit inlets Yes

Dimensions

Height 688 mm

Width 352 mm

Depth 97.50 mm

Built-in height 652 mm

Built-in width 318 mm

Cover, door

Number of cabinet doors 1

Dimensions

Built-in depth 72 mm

Cover, door

Number of locks 0

Dimensions

Number of width units 12

Cover, door

Door/cover is transparent Yes

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP40

Safety

Locking type	Snap on lock Without lock
Glow wire test	650 °C

Sustainability

RoHS conform	Yes
--------------	-----