

Product Datasheet

FL730L



FL730L

Steel enclosure, Orion.Tech, plain door 1250x800x300 mm

Technical Features

Dimensions

Height	1250 mm
Width	800 mm
Depth	300 mm
Thickness of sidewall	2 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 8 mm
Impact resistance IK	IK10

Equipment

Number of flange plate openings	2
---------------------------------	---

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

Equipment

Number of rows	1
----------------	---

Cover, door

Number of cabinet doors	1
Door/cover is transparent	No

Electric current

Rated current	630 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----