



SVS411B



**Impulse 1NO Pushbutton + green Indicator light 230VAC QC busbar passing**

**Technical Features**

**Equipment**

Number of INV contacts	0
Number of NC contacts	0
Number of NO contacts	1
With signal lamp	Yes

**Electric current**

Momentary contact current	16 A
Rated current	16 A

**Capacity**

Number of modules	1
-------------------	---

**Dimensions**

Height	83 mm
Width	17.50 mm
Depth	66 mm

**Voltage**

Rated insulation voltage $U_i$	250 V
Rated operational voltage $U_e$	230 - 230 V

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

**Illustrations | Drawings**

