



75142134



**KNX glass sensor 2gang comf, intg bus coupling unit, KNX - TS sensor, glass al.**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Functions**

With room temperature controller Yes

**Power**

Current consumption 12.50 mA

**Dimensions**

Built-in depth	24.20 mm
Built-in depth flush-mounted boxes	27 mm
Height	160 mm
Width	86 mm
Depth	37.70 mm

**Equipment**

Number of actuation points 4

**Controls and indicators**

With LED indication Yes

**Materials**

Colour	Aluminium
RAL code	9006
Material	Aluminium Glass
Surface finish	Glossy Matt

**Accessories**

Has labelling field No

**Screen**

With display No

**Texts**

Function	For switch, push-button, dimmer and shutter functions Blocking function for sensor surface e.g. for cleaning the glass surface
Installation mode	For vertical mounting
Temperature	Additional connection for external temperature sensor Integrated temperature sensor for operation as controller extension unit Temperature measurement via internal Temperature sensor or external communication object

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes