



HI403R

**Modular change-over switch 63A**

**Technical Features**

**Voltage**

Rated operational voltage U <sub>e</sub>	380 - 690 V
Rated insulation voltage U <sub>i</sub>	800 V
Rated impulse withstand voltage U <sub>imp</sub>	8000 V

**Electric current**

Rated current	63 A
Rated short-time withstand current I <sub>cw</sub> IEC 60947	2.50 kA
Rated conditional short-circuit current I <sub>cc</sub> with gI-gG fuses	100 kA

**Power**

Rated operational power under 400 V AC AC1	41000 W
--	---------

**Architecture**

Number of poles	4
Control/operation element	Short rotary handle
Type of pole	4P

**Dimensions**

Height	116 mm
Width	215 mm
Depth	97 mm

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Cover, door**

Interlockable	Yes
---------------	-----

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Capacity**

Number of modules	12
-------------------	----

**Power**

Total power loss under I <sub>N</sub>	3.60 W
---------------------------------------	--------

**Use conditions**

Operating temperature	-20 - 70 °C
-----------------------	-------------

**Connection**

Cross-section rigid conductor	4 - 50 mm <sup>2</sup>
-------------------------------	------------------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes