

# Product Datasheet

## LNH2160M



LNH2160M

### HRC LV fuse NH2C gG AC500V 160A double indicator with live gripping-lugs

#### Technical Features

##### Architecture

Curve	gG
-------	----

##### Fuse

Fuse size	NH2C
Fuse characteristics	gG

##### Voltage

Type voltage supply	AC/DC
Rated operational voltage Ue	500 - 500 V
Rated voltage at AC 50 Hz	500 - 500 V

##### Electric current

Rated current	160 A
---------------	-------

##### Use conditions

Insulated	No
-----------	----

##### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
---	--------

##### Power

Total power loss under IN	15 W
---------------------------	------

##### Dimensions

Height	150 mm
Width	39 mm
Depth	72.5 mm

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes