



52066089

Call button frame, Q.1, p. white velvety

Technical Features

Voltage

Operating voltage 24 - 24 V

Materials

Colour Polar white

RAL code 9010

Surface finish Velvety

Dimensions

Height 80.50 mm

Width 80.50 mm

Depth 30 mm

Built-in depth 15.80 mm

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -5 - 40 °C

Texts

Installation mode Centre plate for plug-in fixing

Type of connection With screw terminals

Lighting With reassurance lamp

Suitable for

Q.x

Sustainability

REACH-SVHC free Yes

RoHS conform Yes